

D4-16TA Cut Sheet



DirectLOGIC DL405 discrete output module, 16-point, 24-240 VAC, 2 isolated common(s), 8 point(s) per common, 0.5A/point, 3A/common. Removable terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/D4-16TA>

Technical Specifications

Brand	DirectLOGIC
Item	Output module
I/O Module Type	Discrete
Series	DL405
Number of Output Points	16
Nominal Output Voltage	24-240 VAC
Number of Isolated Output Commons	2
Number of Points per Common	8
Load Current	0.5A/point, 3A/common
Fuse Type	Non-replaceable fuse
Includes	Removable terminal block
Programming Software	DirectSOFT programming software v4.0 or later

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/D4-16TA.pdf>
See store item page for other formats.