

# D4-16TR Cut Sheet



DirectLOGIC DL405 relay output module, 16-point, 6-24 VDC/6-240 VAC, (16) Form A, 2 isolated common(s), 8 point(s) per common, 1A/point, 5A/common. Removable terminal block included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/D4-16TR>

## Technical Specifications

Brand	DirectLOGIC
Item	Output module
I/O Module Type	Relay
Series	DL405
Number of Output Points	16
Nominal Output Voltage	6-24 VDC/6-240 VAC
Relay Configuration	(16) Form A (SPST) relays
Number of Isolated Commons	2

Jumper Selectable Isolation	No
Number of Points per Common	8
Load Current	1A/point, 5A/common
Fuse Type	Non-replaceable fuse
Includes	Removable terminal block
Programming Software	DirectSOFT programming software v4.0 or later

## Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/D4-16TR.pdf>  
See store item page for other formats.