

# D4-64TD1 Cut Sheet



DirectLOGIC DL405 discrete output module, 64-point, 5-24 VDC, sinking, 8 common(s), 8 point(s) per common, 0.1A/point, 1A/common, 8A/module. Requires ZIPLink pre-wired cable.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/D4-64TD1>

## Technical Specifications

Brand	DirectLOGIC
Item	Output module
I/O Module Type	Discrete
Series	DL405
Number of Output Points	64
Nominal Output Voltage	5-24 VDC
Discrete Output Type	Sinking
Number of Non-Isolated Output Commons	8

Number of Points per Common	8
Load Current	0.1A/point, 1A/common, 8A/module
Fuse Type	User-supplied external fuse
Requires	ZIPLink pre-wired cable
Programming Software	DirectSOFT programming software v4.0 or later

## Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/D4-64TD1.pdf>  
See store item page for other formats.