

D4-RM Cut Sheet



DirectLOGIC DL405 remote I/O module, 1 port, (1) RS-485 port(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/D4-RM>

Technical Specifications

Brand	DirectLOGIC
Item	Remote I/O module
Series	DL405
Number of Ports	1
Communication Port and Connection Type(s)	(1) RS-485
Port Protocol(s)	<ul style="list-style-type: none">• RM-NET Remote Master• serial remote I/O
Port Speed(s)	19.2 Kb or 38.4 Kb (switch selectable)
Programming Software	DirectSOFT programming software v4.0 or later

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/D4-RM.pdf>
See store item page for other formats.