

D5291S Cut Sheet



gmi process safety relay, energized to trip, 1-channel, loop powered, (1) N.C. or (1) N.O. safety output(s), 10A, (1) N.O. or (1) N.C. monitoring output(s), pluggable screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/D5291S>

Technical Specifications

Brand	gmi
Item	Process safety relay
Relay Type	Energized to trip
Number Of Channels	1
Control Voltage	Loop powered
Safety Output Type	(1) N.C. or (1) N.O.
Safety Contact Load Current	10A
Monitoring Output Type	(1) N.O. or (1) N.C.
Connection	Pluggable screw terminals

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	FM Certification and Control Drawing

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/D5291S.pdf>
See store item page for other formats.