

# DC-BRS12-10 Cut Sheet



SureMotion bore reducer, clamping, stainless steel body, 3/4in outside diameter, 5/8in inside diameter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DC-BRS12-10>

## Technical Specifications

Brand	SureMotion
Item	Bore reducer
Bore Reducer Type	Clamping
Material	Stainless steel
Outside Diameter	3/4in
Inside Diameter	5/8in

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/DC-BRS12-10.pdf>  
See store item page for other formats.