

# DC-BRS14-16M Cut Sheet



SureMotion bore reducer, clamping, stainless steel body, 7/8in outside diameter, 16mm inside diameter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DC-BRS14-16M>

---

## Technical Specifications

|                          |                 |
|--------------------------|-----------------|
| <b>Brand</b>             | SureMotion      |
| <b>Item</b>              | Bore reducer    |
| <b>Bore Reducer Type</b> | Clamping        |
| <b>Material</b>          | Stainless steel |
| <b>Outside Diameter</b>  | 7/8in           |
| <b>Inside Diameter</b>   | 16mm            |

---

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |