

# DC-BRS14-16M Cut Sheet



SureMotion bore reducer, clamping, stainless steel body, 7/8in outside diameter, 16mm inside diameter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DC-BRS14-16M>

## Technical Specifications

<b>Brand</b>	SureMotion
<b>Item</b>	Bore reducer
<b>Bore Reducer Type</b>	Clamping
<b>Material</b>	Stainless steel
<b>Outside Diameter</b>	7/8in
<b>Inside Diameter</b>	16mm

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/DC-BRS14-16M.pdf>  
See store item page for other formats.