

DC-BRS20-17 Cut Sheet



SureMotion bore reducer, clamping, stainless steel body, 1-1/4in outside diameter, 1-1/16in inside diameter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DC-BRS20-17>

Technical Specifications

Brand	SureMotion
Item	Bore reducer
Bore Reducer Type	Clamping
Material	Stainless steel
Outside Diameter	1-1/4in
Inside Diameter	1-1/16in

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document