

DC-DAC57-10 Cut Sheet



SureMotion drive coupling hub, Oldham, aluminum alloy, clamp, size 57, 5/8in bore. Requires DC-DDS57 torque disc.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DC-DAC57-10>

Technical Specifications

Brand	SureMotion
Item	Drive coupling hub
Coupling Type	Oldham
Material	Aluminum alloy
Rated Torque	44.1 N-m
Maximum Angular Misalignment	3.0 degrees
Maximum Parallel Misalignment	0.51mm

Maximum RPM	3000
Attachment Style	Clamp
Coupling Size	57
Bore Diameter	5/8in
Outside Diameter	57.2mm
Requires	DC-DDS57 torque disc

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DC-DAC57-10.pdf>
See store item page for other formats.