

DC-DAC57-10 Cut Sheet



SureMotion drive coupling hub, Oldham, aluminum alloy, clamp, size 57, 5/8in bore. Requires DC-DDS57 torque disc.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DC-DAC57-10>

Technical Specifications

Brand	SureMotion
Item	Drive coupling hub
Coupling Type	Oldham
Material	Aluminum alloy
Rated Torque	44.1 N·m
Maximum Angular Misalignment	3.0 degrees
Maximum Parallel Misalignment	0.51mm

Maximum RPM	3000
Attachment Style	Clamp
Coupling Size	57
Overall Length	78mm
Bore Diameter	5/8in
Outside Diameter	57.2mm
Requires	DC-DDS57 torque disc

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DC-DAC57-10.pdf>
See store item page for other formats.