

DC-DAC57-19M Cut Sheet



SureMotion drive coupling hub, Oldham, aluminum alloy, clamp, size 57, 19mm bore. Requires DC-DDS57 torque disc.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DC-DAC57-19M>

Technical Specifications

| | |
|--------------------------------------|--------------------|
| Brand | SureMotion |
| Item | Drive coupling hub |
| Coupling Type | Oldham |
| Material | Aluminum alloy |
| Rated Torque | 44.1 N-m |
| Maximum Angular Misalignment | 3.0 degrees |
| Maximum Parallel Misalignment | 0.51mm |

| | |
|-------------------------|----------------------|
| Maximum RPM | 3000 |
| Attachment Style | Clamp |
| Coupling Size | 57 |
| Bore Diameter | 19mm |
| Outside Diameter | 57.2mm |
| Requires | DC-DDS57 torque disc |

Agency Approvals

| | |
|-----------------------------|----------------------------------------|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DC-DAC57-19M.pdf>
See store item page for other formats.