

DC-DLSS20-04 Cut Sheet



SureMotion drive coupling, double loop, stainless steel, setscrew, size 20, 1/4in bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DC-DLSS20-04>

Technical Specifications

Brand	SureMotion
Item	Drive coupling
Coupling Type	Double loop
Material	Stainless steel
Rated Torque	7.8 N-m
Maximum Angular Misalignment	15 degrees
Maximum Parallel Misalignment	3.2mm
Maximum RPM	3000
Attachment Style	Setscrew
Coupling Size	20
Bore Diameter	1/4in
Outside Diameter	48mm

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DC-DLSS20-04.pdf>
See store item page for other formats.