

DC-DLSS30-10 Cut Sheet



SureMotion drive coupling, double loop, stainless steel, setscrew, size 30, 5/8in bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DC-DLSS30-10>

Technical Specifications

Brand	SureMotion
Item	Drive coupling
Coupling Type	Double loop
Material	Stainless steel
Rated Torque	5 N-m
Maximum Angular Misalignment	15 degrees
Maximum Parallel Misalignment	3.2mm
Maximum RPM	3000
Attachment Style	Setscrew
Coupling Size	30
Bore Diameter	5/8in
Outside Diameter	54.1mm

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document