

# DC-DLSS40-08 Cut Sheet



SureMotion drive coupling, double loop, stainless steel, setscrew, size 40, 1/2in bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DC-DLSS40-08>

## Technical Specifications

<b>Brand</b>	SureMotion
<b>Item</b>	Drive coupling
<b>Coupling Type</b>	Double loop
<b>Material</b>	Stainless steel
<b>Rated Torque</b>	10 N-m
<b>Maximum Angular Misalignment</b>	15 degrees
<b>Maximum Parallel Misalignment</b>	3.2mm
<b>Maximum RPM</b>	3000
<b>Attachment Style</b>	Setscrew
<b>Coupling Size</b>	40
<b>Bore Diameter</b>	1/2in
<b>Outside Diameter</b>	55.9mm

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/DC-DLSS40-08.pdf>  
See store item page for other formats.