

DC-DLSS40-14M Cut Sheet



SureMotion drive coupling, double loop, stainless steel, setscrew, size 40, 14mm bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DC-DLSS40-14M>

Technical Specifications

Brand	SureMotion
Item	Drive coupling
Coupling Type	Double loop
Material	Stainless steel
Rated Torque	10 N-m
Maximum Angular Misalignment	15 degrees
Maximum Parallel Misalignment	3.2mm
Maximum RPM	3000
Attachment Style	Setscrew
Coupling Size	40
Bore Diameter	14mm
Outside Diameter	55.9mm

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DC-DLSS40-14M.pdf>
See store item page for other formats.