

DC-SBS19-0404 Cut Sheet



SureMotion drive coupling, servo-beam, stainless steel, setscrew, size 19, 1/4in bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DC-SBS19-0404>

Technical Specifications

Brand	SureMotion
Item	Drive coupling
Coupling Type	Servo-beam
Material	Stainless steel
Rated Torque	1.4 N-m
Maximum Angular Misalignment	7.0 degrees
Maximum Parallel Misalignment	0.51mm
Maximum RPM	10000
Attachment Style	Setscrew
Coupling Size	19
Bore Diameter	1/4in
Outside Diameter	19.1mm

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DC-SBS19-0404.pdf>
See store item page for other formats.