

# DC-SBS38-1212 Cut Sheet



SureMotion drive coupling, servo-beam, stainless steel, setscrew, size 38, 3/4in bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DC-SBS38-1212>

## Technical Specifications

<b>Brand</b>	SureMotion
<b>Item</b>	Drive coupling
<b>Coupling Type</b>	Servo-beam
<b>Material</b>	Stainless steel
<b>Rated Torque</b>	8.5 N-m
<b>Maximum Angular Misalignment</b>	7.0 degrees
<b>Maximum Parallel Misalignment</b>	0.76mm
<b>Maximum RPM</b>	5000
<b>Attachment Style</b>	Setscrew
<b>Coupling Size</b>	38
<b>Bore Diameter</b>	3/4in
<b>Outside Diameter</b>	38.1mm

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/DC-SBS38-1212.pdf>  
See store item page for other formats.