

DC-SBS44-1414 Cut Sheet



SureMotion drive coupling, servo-beam, stainless steel, setscrew, size 44, 7/8in bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DC-SBS44-1414>

Technical Specifications

Brand	SureMotion
Item	Drive coupling
Coupling Type	Servo-beam
Material	Stainless steel
Rated Torque	15.3 N-m
Maximum Angular Misalignment	7.0 degrees
Maximum Parallel Misalignment	1.02mm
Maximum RPM	5000
Attachment Style	Setscrew
Coupling Size	44
Bore Diameter	7/8in
Outside Diameter	44.5mm

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DC-SBS44-1414.pdf>
See store item page for other formats.