

DC-SBS63-2020 Cut Sheet



SureMotion drive coupling, servo-beam, stainless steel, setscrew, size 63, 1-1/4in bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DC-SBS63-2020>

Technical Specifications

Brand	SureMotion
Item	Drive coupling
Coupling Type	Servo-beam
Material	Stainless steel
Rated Torque	33.9 N-m
Maximum Angular Misalignment	7.0 degrees
Maximum Parallel Misalignment	1.52mm
Maximum RPM	3750
Attachment Style	Setscrew
Coupling Size	63
Bore Diameter	1-1/4in
Outside Diameter	63.5mm

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document