


DC1562 Cut Sheet



Bryant deluxe strain relief grip, accepts cable diameter size 1.56 to 1.68in, straight 2in NPT male thread fitting, stainless steel mesh, 10in length, indoor and outdoor applications.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DC1562>

Technical Specifications

Brand	Bryant
Item	Cord grip
Grip Type	Strain relief
Application	Deluxe
Low Tension	No
Cable Diameter Size	1.56 to 1.68in
Thread Size	Straight 2in NPT male thread fitting
Mesh Material	Stainless steel
Mesh Length	10in
Body Material	Aluminum
Collar Material	Aluminum
Bushing Material	Neoprene
Environmental Requirements	Indoor and outdoor applications

Agency Approvals

UL Listed File #	E167220
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	701228
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DC1562.pdf>
See store item page for other formats.