

# DD51-AN-0.050-D12 Cut Sheet



Elesa position indicator, 4-digit mechanical, inclined upper, 0.050 counts per revolution, clockwise, 1/2in mounting hole size, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DD51-AN-0.050-D12>

## Technical Specifications

<b>Brand</b>	Elesa
<b>Item</b>	Position indicator
<b>Display Size</b>	4-digit
<b>Display Type</b>	Mechanical
<b>Display Orientation</b>	Inclined upper
<b>Display Units</b>	Counts per revolution
<b>Counts Per Revolution</b>	0.050
<b>Count Direction</b>	Clockwise

<b>Mounting Hole Size</b>	1/2in
<b>Mounting Orientation</b>	Universal
<b>IP Rating</b>	IP65
<b>Color</b>	Orange
<b>Housing Material</b>	Polyamide
<b>Mounting Boss Material</b>	Black oxide steel
<b>Operating Temperature</b>	0 to 50 deg C

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/DD51-AN-0.050-D12.pdf>  
See store item page for other formats.