

DD51-AN-001.0-S Cut Sheet



Elesa position indicator, 4-digit mechanical, inclined upper, 001.0 counts per revolution, counter clockwise, 14mm mounting hole size, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DD51-AN-001.0-S>

Technical Specifications

Brand	Elesa
Item	Position indicator
Display Size	4-digit
Display Type	Mechanical
Display Orientation	Inclined upper
Display Units	Counts per revolution
Counts Per Revolution	001.0
Count Direction	Counter clockwise

Mounting Hole Size	14mm
Mounting Orientation	Universal
IP Rating	IP65
Color	Orange
Housing Material	Polyamide
Mounting Boss Material	Black oxide steel
Operating Temperature	0 to 50 deg C

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/DD51-AN-001.0-S.pdf>
See store item page for other formats.