

DD52R-AN-0001.0-D34 Cut Sheet



Elesa position indicator, 5-digit mechanical, inclined upper, 0001.0 counts per revolution, clockwise, 3/4in mounting hole size, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DD52R-AN-0001.0-D34>

Technical Specifications

| | |
|------------------------------|-----------------------|
| Brand | Elesa |
| Item | Position indicator |
| Display Size | 5-digit |
| Display Type | Mechanical |
| Display Orientation | Inclined upper |
| Display Units | Counts per revolution |
| Counts Per Revolution | 0001.0 |
| Count Direction | Clockwise |

| | |
|-------------------------------|-------------------|
| Mounting Hole Size | 3/4in |
| Mounting Orientation | Universal |
| IP Rating | IP65 |
| Color | Orange |
| Housing Material | Polyamide |
| Mounting Boss Material | Black oxide steel |
| Operating Temperature | 0 to 50 deg C |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/DD52R-AN-0001.0-D34.pdf>
See store item page for other formats.