

DD52R-AR-000.50-D34 Cut Sheet



Elesa position indicator, 5-digit mechanical, inclined lower, 000.50 counts per revolution, clockwise, 3/4in mounting hole size, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DD52R-AR-000.50-D34>

Technical Specifications

Brand	Elesa
Item	Position indicator
Display Size	5-digit
Display Type	Mechanical
Display Orientation	Inclined lower
Display Units	Counts per revolution
Counts Per Revolution	000.50
Count Direction	Clockwise

Mounting Hole Size	3/4in
Mounting Orientation	Universal
IP Rating	IP65
Color	Orange
Housing Material	Polyamide
Mounting Boss Material	Black oxide steel
Operating Temperature	0 to 50 deg C

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/DD52R-AR-000.50-D34.pdf>
See store item page for other formats.