

DD52RE-SST-IP67F34 Cut Sheet



Elesa position indicator, 12mm 6-digit LCD, programmable, 3/4in mounting hole size, IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DD52RE-SST-IP67F34>

Technical Specifications

Brand	Elesa
Item	Position indicator
Display Size	12mm 6-digit
Display Type	LCD
Mounting Hole Size	3/4in
Mounting Orientation	Universal
IP Rating	IP67
Color	Orange
Housing Material	Polyamide
Mounting Boss Material	304 stainless steel
Measurement Type	Programmable
Operating Temperature	0 to 50 deg C

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/DD52RE-SST-IP67F34.pdf>
See store item page for other formats.