

DET.11.2134 Cut Sheet



SapiSelco metal detectable nylon cable tie, 14.17in length, 0.3in width, 110.25 lb tensile strength, 3.98in maximum bundle diameter, blue. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DET.11.2134>

Technical Specifications

Brand	SapiSelco
Item	Cable tie
Cable Tie Type	Metal detectable
Material	Nylon
Length	14.17in
Width	0.3in
Tensile Strength	110.25 lb
Maximum Bundle Diameter	3.98in
Color	Blue
UV Resistant	No
Temperature Rating	-13 to +140 °F
Installation Temperature	+14 °F
Quantity per Pack	100

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document