

# DET.11.2134 Cut Sheet



SapiSelco metal detectable cable tie, 14.17in length, 0.3in width, 132.28lb tensile strength, 3.98in maximum bundle diameter, blue, nylon. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DET.11.2134>

## Technical Specifications

<b>Brand</b>	SapiSelco
<b>Item</b>	Cable tie
<b>Cable Tie Type</b>	Metal detectable
<b>Length</b>	14.17in
<b>Width</b>	0.3in
<b>Tensile Strength</b>	132.28lb
<b>Maximum Bundle Diameter</b>	3.98in
<b>Color</b>	Blue
<b>Material</b>	Nylon
<b>Temperature Rating</b>	-40 to +185 deg F
<b>Quantity per Pack</b>	100

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>