

# DGA-15 Cut Sheet



ProSense differential pressure gauge, 4in dial diameter, 0 to 15.0in of water column, black die-cast aluminum case, aluminum and silicone rubber wetted parts, (2) high and (2) low 1/8in female NPT process connection, panel or surface mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DGA-15>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Differential pressure gauge
<b>Diameter</b>	4in dial
<b>Scale</b>	0 to 15.0in of water column
<b>Case Type</b>	Black die-cast aluminum
<b>Wetted Parts</b>	Aluminum and silicone rubber
<b>Process Connection</b>	(2) high and (2) low 1/8in female NPT
<b>Mounting</b>	Panel or surface

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/DGA-15.pdf>  
See store item page for other formats.