

DIN12-P10 Cut Sheet



Integra DIN rail, slotted, 35mm width, 7mm height, 10.8in length, plated steel. Package of 2. For use with 12in wide Premium series polycarbonate enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DIN12-P10>

Technical Specifications

Brand	Integra
Item	DIN rail
DIN Rail Type	Slotted
Width	35mm
Height	7mm
Length	10.8in
Material	Plated steel
Quantity per Pack	2
For Use With	12in wide Premium series polycarbonate enclosures
Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DIN12-P10.pdf>
See store item page for other formats.