

DL14-00 Cut Sheet



Flowline EchoPod ultrasonic liquid level sensor, 4.1ft/1.25m sensing range, 4-20 mA and (4) SPST relays, N.O./N.C. selectable, 14-28 VDC operating voltage, 1in male NPT process connection.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DL14-00>

Technical Specifications

Brand	Flowline
Item	Level sensor
Series	EchoPod
Sensor Type	Ultrasonic
Media Type	Liquid
Mounting	Vertical top
Process Temperature	20 to 140 deg F
Sensing Range	4.1ft/1.25m
Output	4-20 mA and (4) SPST relays, N.O./N.C. selectable
Operating Voltage	14-28 VDC

Housing Size	2in diameter
Housing Material	Polycarbonate
NEMA Rating	6P
Process Connection	1in male NPT
Electrical Connection	48in integral 9-conductor shielded cable
Includes	Mounting gasket
Requires	An LI99-2001 Fob USB adapter (purchased separately) and WEBCAL software (free download from the AutomationDirect Web site) are required for sensor configuration and firmware updates

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	FM Approval Document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DL14-00.pdf>
See store item page for other formats.