

DL34-00 Cut Sheet



Flowline EchoPod ultrasonic liquid level sensor, 18ft/5.5m sensing range, 4-20 mA and (4) SPST relays, N.O./N.C. selectable, 14-28 VDC operating voltage, 2in male NPT process connection.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DL34-00>

Technical Specifications

| | |
|----------------------------|---|
| Brand | Flowline |
| Item | Level sensor |
| Series | EchoPod |
| Sensor Type | Ultrasonic |
| Media Type | Liquid |
| Mounting | Vertical top |
| Process Temperature | 20 to 140 deg F |
| Sensing Range | 18ft/5.5m |
| Output | 4-20 mA and (4) SPST relays, N.O./N.C. selectable |
| Operating Voltage | 14-28 VDC |

| | |
|------------------------------|---|
| Housing Size | 3.06in diameter |
| Housing Material | Polycarbonate |
| NEMA Rating | 6P |
| Process Connection | 2in male NPT |
| Electrical Connection | 48in integral 9-conductor shielded cable |
| Includes | Mounting gasket |
| Requires | An LI99-2001 Fob USB adapter (purchased separately) and WEBCAL software (free download from the AutomationDirect Web site) are required for sensor configuration and firmware updates |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DL34-00.pdf>
See store item page for other formats.