

DLO2-0BK-1 Cut Sheet



Southwire flexible power cable, unshielded, HDFPC-DLO, RHH/RHW-2 and RW90, single conductor, 2/0 AWG, tinned copper, EPDM thermoset rubber conductor insulation material, black, CPE thermoset rubber jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DLO2-0BK-1>

Technical Specifications

Brand	Southwire
Item	Cable
Wire/Cable Type	Power
UL Wire/Cable Type	HDFPC-DLO, RHH/RHW-2 and RW90
Application	Power
Flexibility	Flexible
Voltage Rating	2000V
Conductors	Single conductor
Conductor Size	2/0 AWG
Conductor Stranding	342-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	EPDM thermoset rubber
Conductor Insulation Color	Black

Shielding	Unshielded
Jacket Material	CPE thermoset rubber
Jacket Color	Black
Nominal Overall Cable Diameter	0.69in
Bulk Length	Cut to length
Package Type	<ul style="list-style-type: none">• 20 to 50ft = Coil• 51 to 80ft = 14 x 7in Reel• 81 to 115ft = 14 x 10in Reel• 116 to 180ft = 16 x 10in Reel• 181 to 250ft = 18 x 10in Reel• 251 to 325ft = 18 x 13in Reel• 326 to 730ft = 24 x 17in Wooden Reel• 731 to 1165ft = 30 x 17in Wooden Reel• 1166 to 2500ft = Large Wooden Reel

Agency Approvals

UL Listed File #	E30117
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	156205
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement