

DLO2BK-1 Cut Sheet



Southwire flexible power cable, unshielded, HDFPC-DLO, RHH/RHW-2 and RW90, single conductor, 2 AWG, tinned copper, EPDM thermoset rubber conductor insulation material, black, CPE thermoset rubber jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DLO2BK-1>

Technical Specifications

Brand	Southwire
Item	Cable
Wire/Cable Type	Power
UL Wire/Cable Type	HDFPC-DLO, RHH/RHW-2 and RW90
Application	Power
Flexibility	Flexible
Voltage Rating	2000V
Conductors	Single conductor
Conductor Size	2 AWG
Conductor Stranding	161-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	EPDM thermoset rubber
Conductor Insulation Color	Black

Shielding	Unshielded
Jacket Material	CPE thermoset rubber
Jacket Color	Black
Nominal Overall Cable Diameter	0.495in
Bulk Length	Cut to length
Package Type	1 to 50ft = Coil, 51 to 150ft = 14 x 7in Reel, 151 to 220ft = 14 x 10in Reel, 221 to 330ft = 16 x 10in Reel, 331 to 470ft = 18 x 10in Reel, 471 to 610ft = 18 x 13in Reel, 611 to 1310ft = 24 x 17in Wooden Reel, 1311 to 2160ft = 30 x 17in Wooden Reel, 2161 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E30117
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	156205
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement