

DLO4BK-1 Cut Sheet



Southwire flexible power cable, unshielded, HDFPC-DLO, RHH/RHW-2 and RW90, single conductor, 4 AWG, tinned copper, EPDM thermoset rubber conductor insulation material, black, CPE thermoset rubber jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DLO4BK-1>

Technical Specifications

Brand	Southwire
Item	Cable
Wire/Cable Type	Power
UL Wire/Cable Type	HDFPC-DLO, RHH/RHW-2 and RW90
Application	Power
Flexibility	Flexible
Voltage Rating	2000V
Conductors	Single conductor
Conductor Size	4 AWG
Conductor Stranding	105-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	EPDM thermoset rubber
Conductor Insulation Color	Black

Shielding	Unshielded
Jacket Material	CPE thermoset rubber
Jacket Color	Black
Nominal Overall Cable Diameter	0.44in
Bulk Length	Cut to length
Package Type	1 to 50ft = Coil, 51 to 200ft = 14 x 7in Reel, 201 to 280ft = 14 x 10in Reel, 281 to 440ft = 16 x 10in Reel, 441 to 630ft = 18 x 10in Reel, 631 to 810ft = 18 x 13in Reel, 811 to 1750ft = 24 x 17in Wooden Reel, 1751 to 2890ft = 30 x 17in Wooden Reel, 2891 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E30117
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	156205
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement