

DME-00-1A Cut Sheet



AutomationDirect photoelectric sensor, tubular, threaded, metal housing, through-beam emitter, infrared, 4m sensing distance, 10-30 VDC operating voltage, 3-wire, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DME-00-1A>

Technical Specifications

| | | | |
|------------------|---------------------------|---------------------|-------------------|
| Brand | AutomationDirect | Operating Voltage | 10-30 VDC |
| Item | Photoelectric sensor | Number of Wires | 3 |
| Shape | Tubular | Sensing Distance | 4m |
| Barrel Type | Threaded | Light Emission (NP) | Infrared |
| Housing Size | 12mm diameter x 55mm body | Cable Length | 6.5ft/2m |
| IP Rating | IP67 | Connection | Pigtail |
| Housing Material | Metal | Conductor Size | 24 AWG |
| Sensing Method | Through-beam emitter | Includes | Mounting hardware |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E187310 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |