

# DME-00-1H Cut Sheet



AutomationDirect photoelectric sensor, tubular, threaded, metal housing, through-beam emitter, infrared, 4m sensing distance, 10-30 VDC operating voltage, NPN, 3-wire, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DME-00-1H>

## Technical Specifications

Brand	AutomationDirect
Item	Photoelectric sensor
Shape	Tubular
Barrel Type	Threaded
Housing Size	12mm diameter x 66mm body
IP Rating	IP67
Housing Material	Metal
Sensing Method	Through-beam emitter

Operating Voltage	10-30 VDC
Number of Wires	3
Switching Output	NPN
Sensing Distance	4m
Light Emission (NP)	Infrared
Connection	4-pin M12 quick-disconnect
Includes	Mounting hardware
Additional Information	Purchase cable separately

## Agency Approvals

UL Listed File #	E187310
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>