

# DN-11PLUGMN Cut Sheet



DINnector terminal plug, 11-pole, accepts wire size 22-14 AWG, green, 12A, 300V rated (UL), top wire entry with terminal screw 90 degrees from entry. For use with DN-EMXM1 or DN-EMXDV series terminal block. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DN-11PLUGMN>

## Technical Specifications

<b>Brand</b>	DINnector
<b>Item</b>	Terminal plug
<b>Number of Poles</b>	11
<b>Wire Size</b>	22-14 AWG
<b>Color</b>	Green
<b>Amperage Rating</b>	12A
<b>Voltage Rating</b>	300V rated (UL)
<b>Configuration</b>	Top wire entry with terminal screw 90 degrees from entry
<b>For Use With</b>	DN-EMXM1 or DN-EMXDV series terminal block
<b>Quantity per Pack</b>	5

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E179129
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>