

DN-12J6Y Cut Sheet



DINnector terminal block jumper, push-in type, 12-pole, green, 30A, 600V rated (UL). Package of 10. For use with DN-Q8-A or DN-Q8B-A series terminal block.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DN-12J6Y>

Technical Specifications

Brand	DINnector
Item	Terminal block jumper
Jumper Type	Push-in
Number of Poles	12
Color	Green
Amperage Rating	30A
Voltage Rating	600V rated (UL)
Quantity per Pack	10
For Use With	DN-Q8-A or DN-Q8B-A series terminal block

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document