

DN-2JL14-AMN Cut Sheet



DINnector terminal block jumper, push-in type, 2-pole, red, 20A, 300V rated (UL). Package of 25. For use with DN-TL14-A, DN-TL14S-A, DN-TL14SLP or DN-14SLN-A series terminal block.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DN-2JL14-AMN>

Technical Specifications

Brand	DINnector
Item	Terminal block jumper
Jumper Type	Push-in
Number of Poles	2
Color	Red
Amperage Rating	20A
Voltage Rating	300V rated (UL)
Quantity per Pack	25
For Use With	DN-TL14-A, DN-TL14S-A, DN-TL14SLP or DN-14SLN-A series terminal block

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/DN-2JL14-AMN.pdf>
See store item page for other formats.