

# DN-2JL14B-AMN Cut Sheet



DINnector terminal block jumper, push-in type, 2-pole, blue, 20A, 300V rated (UL). Package of 25. For use with DN-TL14-A, DN-TL14S-A, DN-TL14SLP or DN-14SLN-A series terminal block.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DN-2JL14B-AMN>

## Technical Specifications

<b>Brand</b>	DINnector
<b>Item</b>	Terminal block jumper
<b>Jumper Type</b>	Push-in
<b>Number of Poles</b>	2
<b>Color</b>	Blue
<b>Amperage Rating</b>	20A
<b>Voltage Rating</b>	300V rated (UL)
<b>Quantity per Pack</b>	25
<b>For Use With</b>	DN-TL14-A, DN-TL14S-A, DN-TL14SLP or DN-14SLN-A series terminal block

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>