

DN-3J4Y Cut Sheet



DINnector terminal block jumper, push-in type, 3-pole, yellow, 25A, 600V rated (UL). Package of 100. For use with DN-T10-A, DN-D10-A, DN-M10-A and DN-Q10-A series terminal block.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DN-3J4Y>

Technical Specifications

| | |
|--------------------------|---|
| Brand | DINnector |
| Item | Terminal block jumper |
| Jumper Type | Push-in |
| Number of Poles | 3 |
| Color | Yellow |
| Amperage Rating | 25A |
| Voltage Rating | 600V rated (UL) |
| Quantity per Pack | 100 |
| For Use With | DN-T10-A, DN-D10-A, DN-M10-A and DN-Q10-A series terminal block |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |