

# DN-CT-RBY Cut Sheet



AutomationDirect wire crimping tool, oval profile, 20-10 AWG capacity, compatible with insulated connectors.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DN-CT-RBY>

## Technical Specifications

Brand	AutomationDirect
Item	Wire crimping tool
Self-adjusting	No
Rotatable Die	No
Crimp Profile	Oval
Crimp Length	9.15mm/0.36in and 12mm/0.47in
Capacity	20-10 AWG
Compatible Connector	Insulated connectors
Handle Type	Comfort grip handles
Overall Length	10in
Material	High-strength alloy steel

## Agency Approvals

UL Listed File #	none
UL Recognized File #	none
UL Hazardous File #	none
CSA File #	none
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>