

DN-CT-SET Cut Sheet



AutomationDirect wire crimping tool set, 24-4 AWG capacity, compatible with insulated terminals and splices and insulated and non-insulated wire ferrules, includes (1) DN-CT-HDL handle and (3) die sets: DN-CT-D2, DN-CT-D4 and DN-CT-D5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DN-CT-SET>

Technical Specifications

Brand	AutomationDirect
Item	Wire crimping tool set
Self-adjusting	No
Rotatable Die	No
Capacity	24-4 AWG
Compatible Connector	Insulated terminals and splices and insulated and non-insulated wire ferrules
Handle Type	Plastic coated handles
Overall Length	9in
Set Includes	(1) DN-CT-HDL handle and (3) die sets: DN-CT-D2, DN-CT-D4 and DN-CT-D5
Additional Information	Purchase additional DN-CT-Dx die sets separately

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document