

# DN-CT-TC2 Cut Sheet



AutomationDirect wire crimping tool, trapezoidal profile, 6-4 AWG capacity, compatible with insulated and non-insulated wire ferrules.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DN-CT-TC2>

## Technical Specifications

<b>Brand</b>	AutomationDirect
<b>Item</b>	Wire crimping tool
<b>Self-adjusting</b>	No
<b>Rotatable Die</b>	No
<b>Crimp Profile</b>	Trapezoidal
<b>Crimp Length</b>	14.5mm/0.57in
<b>Capacity</b>	6-4 AWG
<b>Compatible Connector</b>	Insulated and non-insulated wire ferrules
<b>Handle Type</b>	Comfort grip handles
<b>Overall Length</b>	10in
<b>Material</b>	High-strength alloy steel

## Agency Approvals

<b>UL Listed File #</b>	none
<b>UL Recognized File #</b>	none
<b>UL Hazardous File #</b>	none
<b>CSA File #</b>	none
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>