

# DN-F10L220 Cut Sheet



DINnector screw circuit protection terminal block, blown fuse indicator, accepts wire size 24-10 AWG, gray, 6.3A, 220 VAC/VDC LED indicator(s), 35mm DIN rail mount, 10kA SCCR. Package of 10. For use with GMA, GMC, S500 and S506 series fuses.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DN-F10L220>

## Technical Specifications

<b>Brand</b>	DINnector
<b>Item</b>	Terminal block
<b>Connector Type</b>	Screw
<b>Terminal Block Type</b>	Circuit protection
<b>Terminal Block Special Feature(s)</b>	Blown fuse indicator
<b>Accepts Fuse Class</b>	Small dimension (5x20mm and 5x25mm)
<b>Wire Size</b>	24-10 AWG
<b>Color</b>	Gray

<b>Amperage Rating</b>	6.3A
<b>Voltage Rating</b>	250 VAC/VDC
<b>Indicator</b>	220 VAC/VDC LED
<b>Mounting</b>	35mm DIN rail
<b>SCCR Rating</b>	10kA SCCR
<b>Quantity per Pack</b>	10
<b>For Use With</b>	GMA, GMC, S500 and S506 series fuses

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E179129
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/DN-F10L220.pdf>  
See store item page for other formats.