

# DN-F6L24 Cut Sheet



DINnecter screw circuit protection terminal block, blown fuse indicator, accepts wire size 20-6 AWG, gray, 30A, 24 VAC/VDC LED indicator(s), 35mm DIN rail mount, 10kA SCCR. Package of 10. For use with ABC, AGC, MDA and MDL series fuses.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DN-F6L24>

## Technical Specifications

Brand	DINnecter
Item	Terminal block
Connector Type	Screw
Terminal Block Type	Circuit protection
Terminal Block Special Feature(s)	Blown fuse indicator
Accepts Fuse Class	Small dimension (1-1/4 x 1/4in)
Wire Size	20-6 AWG
Color	Gray
Amperage Rating	30A
Voltage Rating	600V rated (UL)
Indicator	24 VAC/VDC LED
Mounting	35mm DIN rail
SCCR Rating	10kA SCCR
Quantity per Pack	10
For Use With	ABC, AGC, MDA and MDL series fuses

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E179129
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>
Other	None