

DN-F6L24 Cut Sheet



DINnector screw circuit protection terminal block, blown fuse indicator, accepts wire size 20-6 AWG, gray, 30A, 24 VAC/VDC LED indicator(s), 35mm DIN rail mount, 10kA SCCR. Package of 10. For use with ABC, AGC, MDA and MDL series fuses.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DN-F6L24>

Technical Specifications

| | |
|-----------------------------------|---------------------------------|
| Brand | DINnector |
| Item | Terminal block |
| Connector Type | Screw |
| Terminal Block Type | Circuit protection |
| Terminal Block Special Feature(s) | Blown fuse indicator |
| Accepts Fuse Class | Small dimension (1-1/4 x 1/4in) |
| Wire Size | 20-6 AWG |
| Color | Gray |

| | |
|-------------------|------------------------------------|
| Amperage Rating | 30A |
| Voltage Rating | 600V rated (UL) |
| Indicator | 24 VAC/VDC LED |
| Mounting | 35mm DIN rail |
| SCCR Rating | 10kA SCCR |
| Quantity per Pack | 10 |
| For Use With | ABC, AGC, MDA and MDL series fuses |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E179129 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |