

DN-F6 Cut Sheet



DINector screw circuit protection terminal block, accepts wire size 20-6 AWG, gray, 30A, 35mm DIN rail mount, 10kA SCCR. Package of 25. For use with ABC, AGC, MDA and MDL series fuses.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DN-F6>

Technical Specifications

Brand	DINector
Item	Terminal block
Connector Type	Screw
Terminal Block Type	Circuit protection
Accepts Fuse Class	Small dimension (1-1/4 x 1/4in)
Wire Size	20-6 AWG
Color	Gray
Amperage Rating	30A
Voltage Rating	600V rated (UL)
Mounting	35mm DIN rail
SCCR Rating	10kA SCCR
Quantity per Pack	25
For Use With	ABC, AGC, MDA and MDL series fuses

Agency Approvals

UL Listed File #	None
UL Recognized File #	E179129
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	None