

DN-FE2-5 Cut Sheet



DINnector screw circuit protection terminal block, accepts wire size 24-12 AWG, gray. Package of 5. 20A when used as a disconnect; 10A when used with a DN-SUPP-nn.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/DN-FE2-5>

Technical Specifications

Brand	DINnector
Item	Terminal block
Connector Type	Screw
Terminal Block Type	Circuit protection
Wire Size	24-12 AWG
Color	Gray
Voltage Rating	300 VAC/VDC
Quantity per Pack	5
Application	20A when used as a disconnect; 10A when used with a DN-SUPP-nn

Agency Approvals

UL Listed File #	None
UL Recognized File #	E179129
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document